

## DIN rail adaptor HSA

### Description

The DIN rail adaptors of the series HSA are for mounting units with panel mount housings on a DIN rail.

When using the adaptors, enough place is left between the housing and the DIN rail for the connecting cables.

### Operation

The complete set consists of 2 adaptors, 4 screws M2x12, 8 washers M2 and eventually 2 additional holders.

Turn the panel mount housing upside down and remove the 2 screws on one side of the back panel.

Fix 1 adaptor with 2 screws M2x12 and 4 washers (each 2 above and below the adaptor) to the housing.

Connect the second adaptor the same way.

Connect the cables and clip the adaptors on the DIN rail.



### Ordering Information

HSA 72 for FAS100

HSA 96 TCE8000 (panel housing)

# Contact

## KEM Headquarter

Liebigstraße 5  
85757 Karlsfeld  
Germany

T. +49/8131/ 59 39 1-0  
F. +49/8131/ 92 60 4

[info@kem-kueppers.com](mailto:info@kem-kueppers.com)

## KEM Service & Repairs

Wetzeller Straße 22  
93444 Bad Kötzing  
Germany

T. +49/9941/ 94 23 0  
F. +49/9941/ 94 23 23

[info@kem-kueppers.com](mailto:info@kem-kueppers.com)



*More distributors & partners can be found at:  
[www.kem-kueppers.com](http://www.kem-kueppers.com)*

Your local partner:



[www.kem-kueppers.com](http://www.kem-kueppers.com)  
[info@kem-kueppers.com](mailto:info@kem-kueppers.com)